

# ANAESTHESIA WORKSTATION

## asteros prima

### Features

- Ergonomic Design
- Available Models: V7 & V7 Plus
- Modes of Ventilation  
V7 & V7 Plus - VCV, SIMV, ACMV  
V7 & V7 Plus - VCV, SIMV, ACMV
- Inbuilt Ventilator with 7" coloured Display Screens
- Low Flow of Anaesthetic Gases
- GSM Absorber for Closed Loop ventilation
- Fully equipped with an array of safety features and alarm systems
- V7 - 2 Gas based system
- V7 Plus - 3 Gas based system



7" Colour Display



Advanced Breathing System



Dual Bracket for Vaporisers



Ample Storage



RADIOLOGY



MONITORING



ANAESTHESIA



VENTILATION



SURGERY



VETERINARY



MEDICAL GASES



MOBILE HEALTHCARE

# ANAESTHESIA WORKSTATION WORKSTATION

asteros  
Prima

## ASTEROS PRIMA- TECHNICAL SPECIFICATIONS

PARAMETER	SPECIFICATION		
Equipment Classification	Class II, Type B		
Power Supply	External Source	100-240 VAC; 50/60 Hz ;1.5A	
	Internal Source	12 VDC, 4000 mAh Li-ion Battery	
Gas Supply	Pipeline Source	Medical Oxygen, Nitrous Oxide & Compressed Air ( 300-600 kPa )	
	Cylinder Source	2X Medical Oxygen & 2X Nitrous Oxide	
Flow Control System	4-tube rotameter with inbuilt hypoxia guard assuring minimum 25% to 33% O2 and intergrated N2O cut-o system when O2 supply pressure < 2 bar		
	2 tubes for Medical Oxygen & 2 tubes for Nitrous Oxide	0 to 1 L/min 0.05L/min Step Change & 1 to 15 L/min 0.5 L/min Step Change	
	V7 - 4 Tube rotameter	V7+ - 5 Tube rotameter	
Vaporiser Mount	Can accommodate maximum two selectatec vaporizers with interlocking mechanism		
Emergency Oxygen Flush	Single handed operable self-closing button with continuous ow of 35 to 75 L/min		
Circle Absorber System	Ascending bellow type with single sodalime chamber, inbuilt APL valve, integrated oxygen sensor, visible inspiratory and expiratory dish-type valves, Bag/Vent toggle for easy switching between ventilator and manual mode, water trap incorporated at expiratory port and provision for AGSS connection. Autoclavable parts include bellow canister, sodalime canister, water trap, inspiratory and expiratory valve cover.		
Ventilator Type	Electronically controlled and pneumatically driven ventilator		
Display Screen (as per model)	V7	7 inch color TFT display	
	V7 Plus		
Functional Keys	Alarm Silence, Standby, Mode Setting, Back.		
Rotary Encoder Knob	To adjust and confirm parameters like ventilation setting & alarm setting.		
Application	Adult & Pediatric		
Real Time Graphics	Waveform	Pressure vs. Time, Flow vs. Time, Volume vs. Time	
	Loop	Pressure vs. Flow, Volume vs. Pressure, Flow vs. Volume	
Ventilation Modes (as per model)	V7	VCV (can be assisted), V-SIMV and Manual	
	V7 Plus	VCV (can be assisted), V-SIMV and Manual	
<b>Ventilation Setting Parameter</b>	<b>Range</b>	<b>Ventilation Monitoring Parameters</b>	<b>Range</b>
Tidal Volume	40~1600 mL	Tidal Volume	0~4000 mL
Respiratory Rate	1~100 bpm	Minute Volume	0~60 L/min
Inspiratory Time	0.2~9.9 sec	Respiratory Rate	0~170 bpm
Inspiratory Pause	0~50 msec	Peak Airway Pressure	0~100 cmH2O
Inspiration to Expiration Ratio	4:1~1:8	Mean Airway Pressure	0~100 cmH2O
Pressure Control	5~60 cmH2O	Positive End Expiratory Pressure	0~50 cmH2O
Positive End Expiratory Pressure	OFF, 3~30 cmH2O	Oxygen Concentration	15~100 %
Pressure Limit	20~100 cmH2O	Dynamic Compliance	0~200 mL/cmH2O
Oxygen Concentration	From Rotameter		
Flow Trigger	0~30 L/min		
Pressure Trigger	0~-20 cmH2O		
Sigh	0~5		
Safety Airway Pressure	≤ 75 cmH2O		
Alarms	Audio-visual alarms are categorized into 2 levels of priority.		
	High Priority Apnea, Apnea > 2 min, Airway Pressure High, Sustained Pressure, O2 Concentration Low, Battery Low, O2 Supply Low.		
	Medium Priority Airway Pressure Low, Minute Volume High, Minute Volume Low, O2 Concentration High, External Power Supply Failure.		
Alarm Silence Time	≤ 120 sec		
Weight	99 Kg (including GSM circle absorber system)		
Dimensions (LxDxH)	813 x 737 x 1372 in mm (including GSM circle absorber system)		
Additional Features Incorporated	Rigid light-weight trolley with one large sized drawers for storage, adjustable middle tray, top space for monitor placement, two AC power sockets, 4" castors for easy mobility, user detachable circle absorber system and emergency oxygen outlet.		
Standard Accessories	AC power cord, High pressure hose with DISS connector for oxygen, nitrous oxide and air, Disposable dual limb patient circuit with dual water traps for adult, Proximal ow sensor with dual sampling tubes, Galvanic oxygen sensor (inbuilt), Battery (inbuilt), Castor wheels (2 with brake, 2 without brake).		
Optional Accessories	Anaesthetic Vaporizer (Isourane/Sevourane) Reusable dual limb patient circuit with dual water traps for adult/pediatric, Disposable dual limb patient circuit for pediatric, Compliance test lung for adult/pediatric, Extra proximal flow sensor.		

\*Specifications, design and / or accessories listed in the catalogue subject to change without prior notice

MANUFACTURED & SERVICED BY  
**MEDION HEALTHCARE PVT. LTD.**

Plot No K-49, Opp. A-Solution Co. & Power House, Thakurpada  
Gaon, Additional MIDC, Anand Nagar, Ambarnath (E) – 421506.  
Dist. Thane, Maharashtra, INDIA

Tel.: +91-74100 26561 / 62 | Email: sales@medion.co.in

Website: www.medion.co.in

**MEDION**<sup>®</sup>  
Healthcare

Formerly: Meditronics sales & service Pvt. Ltd.

REPRESENTED BY:

